



Kothe Distilling Technologies

5121 N Ravenswood Ave
IL Chicago
USA
Phone +1 312 878 7766
E-mail info@kothe-distilling.com

www.kothe-distilling.com

Quote Number QU01520

Pos	Qty	Item	List Price	Sub Total	Total
1	1,00	1000l - K1200 Standard Potstill Base System Potstill Model K1200 According to European Regulation 97/23/EG Potstill, 1200mm in diameter, made of special high quality copper material, highly-polished and smooth (quality according to hammered copper), 4mm strong. Fill capacity: 1000l (about 265 US gallons) Fill opening: 400mm in diameter Discharge 200mm in diameter and 4" ball valve Indirect heating: steam bath covered in stainless steel and insulated or water bath covered in stainless steel and insulated Stainless steel condenser: made of V4A material, 2200mm in diameter, 1500mm high with automatic cooling with a thermostatic regulator valve. Safety features: overflow, vacuum-breaker, pressure gauge (manometer analog standard, digital on request), auto-air-out, steam trap and dirt filter. Spirit piping, outflow device for distillate and water installation: completely made of stainless steel.	56.000,00	56.000,00	56.000,00
2	1,00	Exclusive Line Setup Whiskey shaped helmet: connected using stainless steel flanging without visible screws or gaskets inside or outside. 800mm in diameter and about 800mm high, with viewing glasses and thermometer. Inside spirit piping Cooling water collection tank as base for the column Side mounted distillation column	10.000,00	10.000,00	10.000,00
3	4,00	Bubblecap Superaromator (special distillation column) 400-500mm in diameter Bubblecaps: new construction with increased copper surface and turbulent motion of liquid. Free adjustable fluid level on distillation plates - flexible adjustment of alcohol content and aroma of distilled mash. Including a pre-condenser in the head of the column (dephlegmator) Inspection-glasses: 4 viewing windows of NW 125mm in diameter for each bubble cap and mash return.	2.000,00	8.000,00	8.000,00
4	1,00	Agitator > 600l still Agitator 1,5 KW, 150 rpm - complete stainless construction	4.000,00	4.000,00	4.000,00
5	1,00	CIP System stainless steel cleaning in hat, pot and special distillation column (one per bubblecap); spray balls in hat and column, rotating nozzles in pot. Max 16bar/8m3 per hour	4.000,00	4.000,00	4.000,00

Beltstraße 3
D-73054 Eisingen
+49 (0)7161/817275
Internet: www.kothe-dt.de

Manager
Ulrich Kothe
Fax +49 (0)7161/817261
E-mail: info@kothe-dt.de

VAT
DE 145 509 888
Handwerksrollen-Nr.:
670 048 526

Account
Kreissparkasse Göppingen
IBAN: DE 8761050000003237454
BIC: GOPS DE 6G

Pos	Qty	Item	List Price	Sub Total	Total
6	1,00	3 Chamber Alcohol Collector Collection tank for heads, hearts and tails Sized according to still size	2.000,00	2.000,00	2.000,00
7	1,00	Top fill opening (additional)	1.000,00	1.000,00	1.000,00
8	1,00	Inspection glasses One per bubblecap and pot	0,00	0,00	0,00
9	1,00	Power Supply Power Supply: 208V 3 Phase	0,00	0,00	0,00
10	1,00	Steam Setup: Float traps Float trap is included with pot for steam setup	0,00	0,00	0,00
11	1,00	Thermometers Analog thermometers standard, digital available One per hat, plate and line arm	0,00	0,00	0,00
12	1,00	Optional Items Lighting - EUR 6.500,00 Lighting of pot and columns Additional viewing windows in the back for lights Lamps and mounting provided Digital Steam Control - EUR 2.500,00 Automation - EUR 19.500,00 Potstill monitoring and management via computer interface and touchscreen INCLUDES all the electronic valves, sensors and software Automation also includes all electric wiring on the still and to the control panel Potstill can be accessed from remote location RJ45 Ethernet access for internet connectivity provided	0,00	0,00	0,00
Subtotals					85.000,00
Discount					
Adjustment					0,00
Grand Total (EUR)					85.000,00

This quote is valid for three months from the date of creation unless grave changes in raw material costs occur.
All orders by Kothe Distilling Technologies directly shall be submitted to Kothe Destillationstechnik and shall be subject to acceptance by Kothe Destillationstechnik.

Payment terms: to be discussed
Inspection: Inspection of still can be performed 10 days prior to shipment from factory.

If you have further questions, please don't hesitate to contact us.

Best regards,

Kothe Distilling Technologies

Beltstraße 3
D-73054 Eisingen
+49 (0)7161/817275
Internet: www.kothe-dt.de

Manager
Ulrich Kothe
Fax +49 (0)7161/817261
E-mail: info@kothe-dt.de

VAT
DE 145 509 888
Handwerksrollen-Nr.:
670 048 526

Account
Kreissparkasse Göppingen
IBAN: DE 8761050000003237454
BIC: GOPS DE 6G